





Selector switch, Harmony 9001K, metal, standard handle, black, 30mm, 3 positions, return both sides to center, 3 C/O

9001KS52BH11



(!) Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony 9001K
Product Or Component Type	Selector switch
Device Short Name	К
Type Of Operator	spring return
Operator Profile	Black standard knob

Complementary

Bezel Material	Metal
Mounting Diameter	1.18 in (30 mm)
Operator Position Information	3 positions
Contacts Type And Composition	3 C/O
Connections - Terminals	Screw-clamp terminals, 1 x 0.222 x 1.5 mm² IEC 60947-1
Device Presentation	Complete product
Cap/Operator Or Lens Colour	Black
Operator Profile	Standard handle
Type Of Operator	Spring return
Size	30 mm
Return	Both sides to centre
Cam Profile	2

Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CSA LR24590 class 3211 03 CE UL listed file F42259 CCN NKCR

Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.44 in (11.271 cm)
Package 1 Width	1.94 in (4.921 cm)
Package 1 Length	2.25 in (5.715 cm)
Package 1 Weight	8.01 oz (227 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov