





# SELECTOR SWITCH 600VAC 10A 30MM T-K

9001KS52K5H13

! Discontinued on: May 6, 2021

! Discontinued

#### Main

| Bezel Material    | Chromium plated metal |
|-------------------|-----------------------|
| Device Short Name | К                     |
| Mounting Diameter | 1.18 in (30 mm)       |

### Complementary

| Line Rated Current            | 10 A                     |
|-------------------------------|--------------------------|
| Key Number                    | E10                      |
| Key Withdrawal Position       | Center                   |
| Operator Position Information | 3 positions              |
| Operator Profile              | Key operated knob        |
| Operator Profile              | 1 projecting push-button |
| Utilisation Category          | AC-15<br>DC-13           |

#### **Environment**

| Nema Degree Of Protection | NEMA 1/2/3/3R/4/6/12/13   |
|---------------------------|---|
| Product Certifications    | UL listed file E42259 CCN NKCR<br>CSA LR24590 class 3211 03<br>CE |

## Ordering and shipping details

| Category          | 21426-9001 K (NOT KA,KM,KX) |
|-------------------|-----------------------------|
| Discount Schedule | CS1                         |
| Returnability     | No                          |
| Country Of Origin | MX                          |

### **Contractual warranty**

Warranty 18 months

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

| Reach Regulation          | REACh Declaration  |
|---------------------------|--|
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)   |
| China Rohs Regulation     | China RoHS declaration   |
| Environmental Disclosure  | Product Environmental Profile  |
| Weee                      | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.   |
| Circularity Profile       | No need of specific recycling operations   |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |