Product data sheet

Specifications





Push-to-test pilot light head, Harmony 9001K, metal, without cap, 30mm, 120V

9001KT38

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 158.00 USD

Main

Range Of Product	Harmony 9001K
Product Or Component Type	Head for push-to-test pilot light
Device Short Name	К

Complementary

Bezel Material	Metal
Mounting Diameter	1.18 in (30 mm)
Cap/Operator Or Lens Colour	Without cap
Bulb Base	BA 9s
Light Block Supply	Full voltage 120 V
Shape Of Screw Head	Round
Light Source	Incandescent bulb
Operating Mode	Push-to-test
[Us] Rated Supply Voltage	120 V
Light Block Supply	Full voltage or resistor
Contacts Type And Composition	1 C/O
Size	30 mm

Environment

Product Certifications	UL listed file E42259 CCN NKCR CSA LR25490 class 3211 03 CE
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901178521
Returnability	No
Country Of Origin	US

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	2.30 in (5.842 cm)
Package 1 Length	4.50 in (11.43 cm)
Package 1 Weight	6.24 oz (176.901 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations Circularity Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov