Product data sheet

Specifications





Push-to-test pilot light head, Harmony 9001K, metal, without cap, 30mm, without bulb, 6V

9001KT40

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 149.00 USD

Μ	ai	in
	a	

Range Of Product	Harmony 9001K
Product Or Component Type	Head for push-to-test pilot light
Device Short Name	К

Complementary

oompiementai y	
Bezel Material	Metal
Mounting Diameter	1.18 in (30 mm)
Cap/Operator Or Lens Colour	Without cap
Bulb Base	BA 9s
Light Block Supply	Direct <= 250 V
Shape Of Screw Head	Round
Light Source	Bulb not included
Operating Mode	Push-to-test
[Us] Rated Supply Voltage	6 V
Light Block Supply	Full voltage
Contacts Type And Composition	1 C/O
Size	30 mm

Environment

Product Certifications	CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR CE
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1

PCE

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	6.40 oz (181.437 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations Circularity Profile