

Product data sheet

Specifications

SQUARE D



complete control station, Harmony 9001K, operators, outdoor indoor installation

9001KYK32

Product availability: Stock - Normally stocked in distribution facility

Price*: 441.00 USD

Main

Range Of Product	Harmony 9001K
Product Or Component Type	Complete control station
Device Short Name	KY
Provided Equipment	Contact block Legend plate
Contact Block Name	KA1

Complementary

Enclosure/Cubicle Description	Surface mounting
Enclosure Material	Die cast zinc alloy Gray
Type Of Installation	Indoor/outdoor
Control Station Composition	2 push-buttons 3 NO + 3 NC UP-DOWN-STOP
Connections - Terminals	Screw-clamp terminals
[Ie] Rated Operational Current Ac	10 A

Environment

Nema Degree Of Protection	NEMA 3/4/13
---------------------------	-------------

Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901040002
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.69 in (11.9 cm)
Package 1 Width	5.31 in (13.5 cm)
Package 1 Length	11.61 in (29.5 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	4.50 lb(US) (2.04 kg)
------------------	-----------------------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov