

Product data sheet

Specifications



Illuminated push-button head, Harmony 9001SK, plastic, plastic guard flush, green, 30mm, spring return, 110-120V

9001SK1L1G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 167.00 USD

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for illuminated push-button
Device Short Name	9001SK

Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Octagonal
Operator Additional Information	Plastic guard
Bulb Base	BA 9s
Light Block Supply	Via transformer 120 V AC 50/60 Hz
Contacts Type And Composition	Without contact block
Product Certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03
Ip Degree Of Protection	IP64
Nema Degree Of Protection	NEMA 1/2/3/3R/4/4X/6/12/13
Cap/Operator Or Lens Colour	Green
[Us] Rated Supply Voltage	110...120 V
Light Block Supply	Via integral transformer
Operator Profile	Flush
Type Of Operator	Spring return
Supply Frequency	50...60 Hz
Size	30 mm
Light Source	Incandescent bulb

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901820932

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
---------------	-----

Country Of Origin	MX
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Number Of Units In Package 1	1
------------------------------	---

Package 1 Height	2.21 in (5.601 cm)
------------------	--------------------

Package 1 Width	3.66 in (9.299 cm)
-----------------	--------------------

Package 1 Length	1.81 in (4.6 cm)
------------------	------------------

Package 1 Weight	6.56 oz (185.973 g)
------------------	---------------------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov