

Product data sheet

Specifications

SQUARE D



Empty enclosure control station,
Harmony 9001K, Harmony
9001SK, stainless steel, 2 cut
outs, 30mm

9001KYSS2

Product availability: Stock - Normally stocked in distribution facility

Price*: 270.00 USD

Main

Range Of Product	Harmony 9001K Harmony 9001SK
Product Or Component Type	Empty enclosure
Device Short Name	9001K
Number Of Cut-Out	2 cut-outs
Cable Entry	1 entry tapped for 3/4" knockout

Complementary

Product Destination	For Ø 30 mm control and signalling units
Material	Stainless steel
Net Weight	3.02 lb(US) (1.37 kg)

Environment

Protective Treatment	TH
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Overvoltage Category	II IEC 61140
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 3 NEMA 4 NEMA 4X

Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901017493
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	5.00 in (12.7 cm)
Package 1 Width	4.80 in (12.192 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	3.07 lb(US) (1.393 kg)
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	19.60 lb(US) (8.891 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)


Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration
California Proposition 65		WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Dimensions

Below drawing shows a 3-hole enclosure. Refer to the product characteristics to get the number of holes



(1) Knockout conduit thread: 3/4".

a		G	
mm	in.	mm	in.
197	7.75	181	7.12