

# Product data sheet

Specifications

SQUARE D



Illuminated push-button head, Harmony 9001SK, plastic, plastic guard flush, red, 30mm, spring return, 24-28V

9001SK1L35R

! Discontinued

! Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for illuminated push-button
Device Short Name	9001SK

## Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Octagonal
Operator Additional Information	Plastic guard
Bulb Base	BA 9s
Light Block Supply	Full voltage 24 V Full voltage 28 V
Contacts Type And Composition	Without contact block
Product Certifications	UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 CE
Ip Degree Of Protection	IP64
Nema Degree Of Protection	NEMA 1/2/3/3R/4/4X/6/12/13
Cap/Operator Or Lens Colour	Red
[Us] Rated Supply Voltage	24...28 V
Light Block Supply	Full voltage
Operator Profile	Flush
Type Of Operator	Spring return
Size	30 mm
Light Source	Incandescent bulb

## Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901040453

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	6.40 oz (181.437 g)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>