Product data sheet

Specifications



30mm push button, Type SK, 2.25 inch red mushroom button, 6A inductive at 120VAC, 1NO/1NC contact, NEMA 4, 4X

9001SKR5R05H13

① Discontinued

() Discontinued on: Oct 9, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Push-button
Device Short Name	9001SK
Operator Additional Information	Snap-in plastic

Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Contacts Type And Composition	1 C/O
Contact Operation	Standard
Mechanical Durability	5000000 cycles
Device Presentation	Complete product
Cap/Operator Or Lens Colour	Red
Operator Profile	Mushroom Ø 57 mm
Type Of Operator	Spring return
Size	30 mm

Environment

Ip Degree Of Protection	IP66
	CSA C22.2 No 14
	UL 508
	EN/IEC 60947-5-4
	JIS C 4520
	EN/IEC 60947-5-1
	JIS C 852
Standards	EN/IEC 60947-1

Nema Degree Of Protection

NEMA 1/2/3/3R/4/4X/6/12/13

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901042914

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	3.20 oz (90.719 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov