Product data sheet

Specifications





Push-button head, Harmony 9001SK, plastic, mushroom 41mm, red, 30mm, 3 positions, return to center

9001SKR8R

Product availability: Stock - Normally stocked in distribution facility

Price*: 86.00 USD

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for push-button
Device Short Name	9001SK

Complementary

Bezel Material	Plastic	
Mounting Diameter	1.18 in (30 mm)	
Shape Of Signaling Unit Head	Octagonal	
Operator Additional Information	Screw-on plastic	
Light Source	without	
Light Block Supply	Supply Without supply	
Contacts Type And Composition	Without contact block	
Product Certifications	CE CSA LR24590 class 3211 03 UL listed file E42259 CCN NKCR	
Ip Degree Of Protection	IP64	
Nema Degree Of Protection	NEMA 1/2/3/3R/4/4X/6/12/13	
Cap/Operator Or Lens Colour	Or Lens Colour Red	
Operator Profile	Mushroom Ø 41 mm	
Type Of Operator	Pull : spring return, center : stay put, push : spring return	
Operator Position Information	sition Information 3 positions	
Size	30 mm	

Ordering and shipping details

Category	US10CS121429	
Discount Schedule	0CS1	
Gtin	785901064541	
Returnability	Yes	
Country Of Origin	MX	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.30 in (5.842 cm)
Package 1 Width	1.80 in (4.572 cm)
Package 1 Length	3.70 in (9.398 cm)
Package 1 Weight	2.72 oz (77.111 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov