





Illuminated push-button, Harmony 9001SK, plastic, mushroom 41mm, red, 30mm, 2 positions, push-pull, 110-120V, 1 C/O

9001SKR9P1R05H13





Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Illuminated push-button
Device Short Name	9001SK
Operator Additional Information	Saraw on plactic

Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Contacts Type And Composition	1 C/O
Contact Operation	Standard
Mechanical Durability	5000000 cycles
Device Presentation	Complete product
Cap/Operator Or Lens Colour	Red
[Us] Rated Supply Voltage	110120 V
Light Block Supply	Via integral transformer
Operator Profile	Mushroom Ø 41 mm
Type Of Operator	Push-pull
Operator Position Information	2 positions
Supply Frequency	5060 Hz
Size	30 mm
Bulb Base	BA 9s
Light Source	Incandescent bulb

Environment

Standards	JIS C 852	
	UL 508	
	EN/IEC 60947-5-4	
	EN/IEC 60947-1	
	JIS C 4520	
	CSA C22.2 No 14	
	EN/IEC 60947-5-1	
Ip Degree Of Protection	IP66	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901043096
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.50 in (6.35 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	4.50 in (11.43 cm)
Package 1 Weight	3.86 lb(US) (1.75 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov