

Product data sheet

Specifications



Illuminated push-button head,
Harmony 9001SK, plastic,
mushroom 41mm, red, 30mm, 2
positions, push-pull, 24-28V

9001SKR9P35R

Product availability: Non-Stock - Not normally stocked in
distribution facility

Price*: 215.00 USD

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for illuminated push-button
Device Short Name	9001SK
Operator Additional Information	Screw-on plastic

Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Contacts Type And Composition	Without contact block
Mechanical Durability	5000000 cycles
Device Presentation	Basic element
Cap/Operator Or Lens Colour	Red
[Us] Rated Supply Voltage	24...28 V
Light Block Supply	Full voltage
Operator Profile	Mushroom Ø 41 mm
Type Of Operator	Push-pull
Operator Position Information	2 positions
Size	30 mm
Bulb Base	BA 9s
Light Source	Incandescent bulb

Environment

Standards	UL 508 JIS C 852 JIS C 4520 EN/IEC 60947-5-1 EN/IEC 60947-1 CSA C22.2 No 14 EN/IEC 60947-5-4
Ip Degree Of Protection	IP66
Nema Degree Of Protection	NEMA 1/2/3/3R/4/4X/6/12/13

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901043140
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	3.52 oz (99.79 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov