

Product data sheet

Specifications



SELECTOR SWITCH 600VAC 10A 30MM SK

9001SKS11BH4

⚠ Discontinued on: Dec 2, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| | |
|---------------------------|-----------------|
| Range Of Product | Harmony 9001SK |
| Product Or Component Type | Selector switch |
| Device Short Name | 9001SK |

Complementary

| | |
|---------------------|------------------|
| Bezel Material | Plastic |
| Mounting Diameter | 1.18 in (30 mm) |
| Device Presentation | Complete product |

Environment

| | |
|---------------------------------------|---|
| Protective Treatment | TC |
| Ambient Air Temperature For Storage | -40...158 °F (-40...70 °C) |
| Ambient Air Temperature For Operation | -13...158 °F (-25...70 °C) |
| Electrical Shock Protection Class | Class II IEC 61140 |
| Ip Degree Of Protection | IP66 IEC 60529 |
| Nema Degree Of Protection | NEMA 1/2/3/3R/4/4X/6/12/13 |
| Product Certifications | CSA LR24590 class 3211 03 CE UL listed file E42259 CCN NKCR |

Ordering and shipping details

| | |
|-------------------|--------------|
| Category | US10CS121429 |
| Discount Schedule | 0CS1 |
| Returnability | No |
| Country Of Origin | MX |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.





[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

| | | |
|---|----------------------------|-----|
|  | Reach Free Of Svhc | |
|  | Toxic Heavy Metal Free | |
|  | Mercury Free | |
|  | Rohs Exemption Information | Yes |

Certifications & Standards

| | |
|---------------------------|--|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |