# **Product data sheet**

Specifications



Selector switch head, Harmony 9001SK, plastic, standard handle, black, 30mm, 3 positions, return both sides to center

9001SKS56B

① Discontinued On: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Or Component Type	Head for selector switch
Device Short Name	К
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Mounting Diameter	1.18 in (30 mm)
Range Of Product	Harmony 9001SK

## Complementary

Bezel Material	Plastic
Cap/Operator Or Lens Colour	black
Contacts Type And Composition	Without contact block
Operator Position Information	3 positions
Operator Profile	Standard handle
Operator Profile	1 projecting push-button
Size	30 mm
Type Of Operator	Spring return both sides to centre
Cap/Operator Or Lens Colour	Black
Type Of Operator	Spring return
Contacts Type And Composition	Without contact block

#### Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product Certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

## Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901044062
Returnability	No

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of Origin	MX

#### **Packing Units**

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.62 in (19.355 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	19.35 in (49.161 cm)
Package 1 Weight	3.20 oz (90.719 g)

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov