Product data sheet

Specifications





Push-to-test pilot light, Harmony 9001SK, plastic, polycarbonate, fresnel lens, red, 30mm, 110...120V

9001SKT1R31

Product availability: Stock - Normally stocked in distribution facility

Price*: 197.00 USD

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Push-to-test pilot light
Lens Type	Fresnel plastic
Light Block Supply	Via transformer 110 V AC 50/60 Hz Via transformer 120 V AC 50/60 Hz

Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Round
Cap/Operator Or Lens Colour	Red
Bulb Base	BA 9s
Operating Mode	Push-to-test
Lens Type	Fresnel
[Us] Rated Supply Voltage	110120 V
Light Block Supply	Via integral transformer
Contacts Type And Composition	1 C/O
Supply Frequency	5060 Hz
Lens Material	Polycarbonate
Size	30 mm
Light Source	Incandescent bulb

Environment

Protective Treatment	TC	
Ip Degree Of Protection	IP66	

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901044420

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	2.40 in (6.096 cm)	
Package 1 Width	2.00 in (5.08 cm)	
Package 1 Length	4.50 in (11.43 cm)	
Package 1 Weight	7.20 oz (204.117 g)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov