Product data sheet

Specifications







Push-to-test pilot light, Harmony 9001SK, plastic, polycarbonate, fresnel, green, 30mm, 24-28V

9001SKT35G31

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 167.00 USD

Main

Range Of Product	Harmony 9001SK	
Product Or Component Type	Push-to-test pilot light	
Lens Type	Fresnel plastic	
Light Block Supply	Full voltage 24 V Full voltage 28 V	

Complementary

Complementary	
Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Round
Cap/Operator Or Lens Colour	Green
Bulb Base	BA 9s
Operating Mode	Push-to-test
Lens Type	Fresnel
[Us] Rated Supply Voltage	2428 V
Light Block Supply	Full voltage
Contacts Type And Composition	1 C/O
Lens Material	Polycarbonate
Size	30 mm
Light Source	Incandescent bulb

Environment

Protective Treatment	тс
Ip Degree Of Protection	IP66

Ordering and shipping details

Category	US10CS121429	
Discount Schedule	0CS1	
Gtin	785901959953	
Returnability	Yes	
Country Of Origin	MX	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	4.16 oz (117.934 g)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

	Toxic Heavy Metal Free	
	Mercury Free	
9	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations Circularity Profile