Specifications



Foot Switch, Harmony 9002AW, industrial, oversized pedal and side shields, SPDT contact, NEMA 2, 4, 13, 5A resistive at 600V AC

9002AW132

Product availability: Stock - Normally stocked in distribution facility

Price*: 750.00 USD

Main

Range	9002AW	
Product	Foot switch	
Contact Operation	1 step	
Certifications	UL Listed CSA	
Cable Entry	0.75 inch NPT conduit entrance	
Contact Arrangement	SPDT	
Enclosure Rating	NEMA 2/4/13	
Voltage Rating	600 V AC/DC	
Protection	Oversized pedal shield Side shield	
Operator Action	Spring return	
Rated Breaking Capacity	15 A 120 V AC inductive control circuit UL 508 10 A 240 V AC inductive control circuit UL 508 6 A 480 V AC inductive control circuit UL 508 5 A 600 V AC inductive control circuit UL 508 15 A 120 V AC resistive control circuit UL 508 0.5 A 125 V DC resistive control circuit UL 508	
Height	6.26 in (159 mm)	
Width	6.42 in (163 mm)	
Depth 8.54 in (217 mm)		

Ordering and shipping details

Category	US10CS121441	
Discount Schedule	0CS1	
Gtin	785901045267	
Returnability	Yes	
Country Of Origin	МХ	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Height	6.50 in (16.5 cm)
Package 1 Width	7.01 in (17.8 cm)
Package 1 Length	11.30 in (28.7 cm)
Package 1 Weight	10.36 lb(US) (4.7 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov