SQUARE D





Foot Switch, Harmony 9002AW, industrial, oversized pedal and side shields, SPDT contact, NEMA 4, 13, two stage, 5A at 600V AC

9002AW134

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 930.00 USD

Main

Range	9002AW
Product	Foot switch
Contact Operation	2 steps
Certifications	CSA
	UL Listed
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPDT per step
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Oversized pedal shield
	Side shield
Operator Action	Spring return
Rated Breaking Capacity	15 A 120 V AC inductive control circuit UL 508
	10 A 240 V AC inductive control circuit UL 508
	6 A 480 V AC inductive control circuit UL 508
	5 A 600 V AC inductive control circuit UL 508
	15 A 120 V AC resistive control circuit UL 508
	0.5 A 125 V DC resistive control circuit UL 508
Height	6.26 in (159 mm)
Width	6.42 in (163 mm)
Depth	8.54 in (217 mm)

Ordering and shipping details

	11 0	
Category	US10CS121441	
Discount Schedule	0CS1	
Gtin	785901044789	
Returnability	No	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	15.24 in (38.71 cm)	
Package 1 Width	6.00 in (15.24 cm)	
Package 1 Length	38.71 in (98.322 cm)	
Package 1 Weight	10.66 lb(US) (4.835 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov