Product data sheet

Specifications



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Pilot light
Device Short Name	9001SK
Lens Type	Fresnel plastic
Light Block Supply	Direct 120 V AC/DC

Complementary

Plastic
1.18 in (30 mm)
Round
Amber
incandescent
BA 9s
120 V AC/DC
7.08 lbf.in (0.8 N.m) EN/IEC 60947-1
Cross slotted
Screw clamp terminals, 1 x 0.222 x 1.5 mm ² EN/IEC 60947-1
10 A
10 A cartridge fuse EN/IEC 60947-5-1
250 V 2)EN/IEC 60947-1
2.5 kV EN/IEC 60947-1
Any position
Push-to-test
2.13 in (54 mm)
2.76 in (70 mm)
1.65 in (42 mm)
0.40 lb(US) (0.181 kg)

Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Electrical Shock Protection Class	Class II IEC 61140
Protective Treatment	TC
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4
	NEMA 4X
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Standards	JIS C 852
	EN/IEC 60947-5-1
	UL 508
	JIS C8201-5-1
	EN/IEC 60947-1
	EN/IEC 60947-5-4
	CSA C22.2 No 14
	JIS C8201-1
Product Certifications	NEMA
	UL 508

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	00785901398776
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

REACh Declaration
Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS declaration
Product Environmental Profile
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
End of Life Information
WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov