





Push-to-test pilot light, Harmony 9001SK, plastic, polycarbonate, domed, red, 30mm, 120V

9001SKT38R9

! Discontinued on: Jun 30, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Push-to-test pilot light
Lens Type	Domed plastic
Light Block Supply	Full voltage 120 V

## Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Round
Cap/Operator Or Lens Colour	Red
Bulb Base	BA 9s
Operating Mode	Push-to-test
Lens Type	Domed
[Us] Rated Supply Voltage	120 V
Light Block Supply	Full voltage or resistor
Contacts Type And Composition	1 C/O
Lens Material	Polycarbonate
Size	30 mm
Light Source	Incandescent bulb

#### **Environment**

Protective Treatment	TC	
Ip Degree Of Protection	IP66	

## Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901960003
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	8.00 oz (226.796 g)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov