





CONTROL STATION + OPERATORS

9001SKY107

- ! Discontinued on: Dec 2, 2020
- ! End-of-service on: Dec 31, 2020

① Discontinued

Main

Range Of Product	Harmony 9001KY	
Product Or Component Type	Control station	
Device Short Name	9001KY	
Provided Equipment	Label plate JOG	
Contact Block Name	KA1	
Product Specific Application	For hoisting and mechanical handling applications	
Level Or Class	Class II Division 2 Group G Class III	

Complementary

Enclosure/Cubicle Description	Wall-mounted enclosure 1 cut-out Ø 30 mm	
Enclosure Material	Polymeric	
Type Of Installation	Indoor/outdoor	
Control Station Composition	1 push-button 1 NO + 1 NC	
Mechanical Interlocking	Without mechanical interlock	
Connector Type	Screw clamp connector	
Connections - Terminals	Direct connection AWG 2) solid stranded Direct connection AWG 12) solid stranded Direct connection AWG 24) solid stranded	
[Ue] Rated Operational Voltage	600 V	
[le] Rated Operational Current Ac	10 A	

Environment

Nema Degree Of Protection	NEMA 3 NEMA 1	
	NEMA 13	
	NEMA 4	
Environmental Characteristic	Resistant against immersion in water Dust and oil resistant	
Product Certifications	UL Listed	
Ambient Air Temperature For Operation	erature For -13140 °F (-2560 °C)	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	21429-9001 SK,SKY	
Discount Schedule	CS1	
Gtin	00785901706861	
Returnability	No	
Country Of Origin	MX	

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov