Product data sheet

Specifications

Green

SQUARE D



Empty enclosure control station, Harmony 9001K, Harmony 9001SK, plastic, 4 cut-outs, 30mm, for 3/4-14 NPT cable entry

9001SKYP4

Product availability: Stock - Normally stocked in distribution facility

Price*: 239.00 USD

Main

| Range Of Product | Harmony 9001K Harmony 9001SK | |
|---------------------------|---------------------------------|--|
| Product Or Component Type | Empty enclosure | |
| Device Short Name | 9001SK | |
| Number Of Cut-Out | 4 cut-outs | |
| Cable Entry | Conduit entries for 3/4"-14 NPT | |

Complementary

| Product Destination | For Ø 30 mm control and signalling units | |
|---------------------|------------------------------------------|--|
| Material | Plastic | |

Environment

| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) |
|------------------------------------------|----------------------|
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C) |

Ordering and shipping details

| Category | US10CS121431 | |
|-------------------|--------------|--|
| Discount Schedule | 0CS1 | |
| Gtin | 785901524618 | |
| Returnability | Yes | |
| Country Of Origin | US | |

Packing Units

| • | |
|------------------------------|-----------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.70 in (9.4 cm) |
| Package 1 Width | 5.31 in (13.5 cm) |
| Package 1 Length | 17.60 in (44.7 cm) |
| Package 1 Weight | 2.67 lb(US) (1.21 kg) |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |