





Foot Switch, Harmony 9002AW, industrial, pedal and side shields, SPDT contact, NEMA 4, 13 enclosure, two stage, 5A at 600V AC

9002AW6

Product availability: Stock - Normally stocked in distribution facility

Price*: 543.00 USD

Main

Range	9002AW
Product	Foot switch
Contact Operation	2 steps
Certifications	UL Listed
	CSA
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPDT per step
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Side shield
	Pedal shield
Operator Action	Spring return
Rated Breaking Capacity	15 A 120 V AC inductive control circuit UL 508
	10 A 240 V AC inductive control circuit UL 508
	6 A 480 V AC inductive control circuit UL 508
	5 A 600 V AC inductive control circuit UL 508
	15 A 120 V AC resistive control circuit UL 508
	0.5 A 125 V DC resistive control circuit UL 508
Height	4.84 in (123 mm)
Width	5.39 in (137 mm)
Depth	9.02 in (229 mm)

Ordering and shipping details

Category	US10CS121441
Discount Schedule	0CS1
Gtin	785901816508
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Pa	ackage 1	PCI
-----------------	----------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	5.60 in (14.224 cm)
Package 1 Width	5.60 in (14.224 cm)
Package 1 Length	12.00 in (30.48 cm)
Package 1 Weight	4.68 lb(US) (2.123 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov