

9013FHG42J59Z22C20

PRESSURE SWITCH 575VAC 1 HP TYPE F+ OPT

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 20.90 USD



! Discontinued

9013FHG42J59Z22C20 has not been replaced. Please contact your customer care center for more information.

Main

Device short name	FHG
Enclosure type	Standard environment enclosure indoor
Product specific application	Control small electrically driven air compressors
Quantity per set	Set of 20
Range of product	Square D Pumptrol
Type of packing	Bulk

Complementary

Adjustable range on rising pressure	100...200 psi
Contact code designation	A600
Depth	2.78 in
Device composition	Black cover
Electrical connection	Screw clamp terminal
Fixing mode	By brackets
Fluid connection type	0.25 inch NPSF internal
Height	2.8 in
Materials in contact with fluid	Nitrile (Buna-N) diaphragm
Maximum pressure	220 psig
Motor power hp	1.5 hp 115 V AC 1 phase 2 hp 115 V AC 3 phases 1 hp 460/575 V AC 3 phases 2 hp 230 V AC 1 phase 3 hp 230 V AC 3 phases
Number of poles	2
Permissible voltage	<= 575 V AC
Pressure actuator	Diaphragm
Pressure setting range	175 psi for off

Product weight	1.13 lb(US)
Scale type	Fixed differential
Switch function	DPST
Width	3.76 in

Environment

Approximate fixed differential	35 psi
NEMA degree of protection	NEMA 1
Product certifications	UL listed file E12158 CCN NKPZ CSA LR25490 class 3211 06

Ordering and shipping details

Category	21531 - 9013 FHG (BULK PACK - DISCOUNT CP7)
Discount Schedule	CP7
GTIN	00785901577591
Nbr. of units in pkg.	20
Package weight(Lbs)	1
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------