

# Product data sheet

Specifications

SQUARE D



Pneumatic Timer, off delay, 0.1 to 60 seconds, 110/120 VAC 50/60 Hz, timed and instantaneous

9050AO12DV02

Discontinued on: Jul 1, 2020

Discontinued

## Main

Product Range	9050A/H
Product Type	Timer
Timing Mode	Off-delay
Timing Range	0.1 s...1 min
Switch Function	SPDT
Coil Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Contact Operation	Time delayed 1 NO + 1 NC Instantaneous 2 NO + 2 NC
Current Rating	15 A

## Complementary

Maximum Switching Voltage	600 V AC
Electrical Connection	Screw-clamp terminals
Reset Response Time	29 ms - on-delay 27 ms - off-delay
Mounting Support	Panel

## Environment

Ambient Temperature Range - Operational	68...104 °F (20...40 °C)
Certifications	UL Listed CSA
Height	2.64 in (67 mm)
Width	4.02 in (102 mm)
Depth	4.37 in (111 mm)

## Ordering and shipping details

Category	21631-9050 A ONE MINUTE PNEUMATIC TIMER
Discount Schedule	CP1
Gtin	00785901962717
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.54 in (6.452 cm)
Package 1 Width	1.00 in (2.54 cm)
Package 1 Length	6.45 in (16.387 cm)
Package 1 Weight	34.95 oz (990.782 g)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information.

California Proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)