





Transformer, Type KL, industrial control, 300VA, 1 phase, 480V primary, 120V secondary, 80C rise

9070KL300D9

Product availability: Stock - Normally stocked in distribution facility

Price*: 831.00 USD

Main

| Product Or Component Type | Industrial Control Transformer |
|---------------------------|--------------------------------|
| Range Of Product | KL |

Complementary

| Phase | 1 phase | |
|-----------------------|-------------------------|--|
| Rated Power In Va | 300 VA | |
| Primary Voltage | 440 V | |
| | 460 V | |
| | 480 V | |
| Secondary Voltage | 120 V | |
| | 115 V | |
| | 110 V | |
| Temperature Rise | 80 °C | |
| Electrical Connection | Screw clamp terminals | |
| Connector Type | Lead 2001.31 ft (610 m) | |

Environment

| Product Certifications | CE UL Listed CSA |
|---------------------------|-------------------------|
| Nema Degree Of Protection | Not rated (open device) |
| Insulation Temperature | 266 °F (130 °C) |

Ordering and shipping details

| Category | US10CP821692 | |
|-------------------|--------------|--|
| Discount Schedule | 0CP8 | |
| Gtin | 785901020240 | |
| Returnability | Yes | |
| Country Of Origin | US | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 6.50 in (16.51 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Package 1 Width | 6.70 in (17.018 cm) | |
|------------------|------------------------|--|
| Package 1 Length | 7.70 in (19.558 cm) | |
| Package 1 Weight | 8.54 lb(US) (3.874 kg) | |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |