





Transformer, Type T, industrial control, 1000VA, 1 phase, 208/230/460V primary, 115V secondary, 115C rise

9070T1000D20

Product availability: Stock - Normally stocked in distribution facility

Price\*: 1,214.00 USD

#### Main

Product Type	Industrial Control Transformer
Туре	Т

### **Complementary**

Number Of Phases	1 phase	
Power Rating	1000 VA UL 1000 VA CSA 1000 VA NOM 630 VA CE	
Primary To Secondary Voltage	e 208/230/460 V 115 V	
Temperature Rise	115 °C	
Electrical Connection	Screw clamp terminals	
Height	6.17 in (156.72 mm)	
Width	7.06 in (179.32 mm)	
Depth	5.92 in (150.37 mm)	
Material	Copper: winding	
Fingersafe Cover Compatibility	afe Cover Compatibility FSC2	

### **Environment**

Certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239
Enclosure Type	Not rated (open device)
Insulation Temperature	356 °F (180 °C)

# Ordering and shipping details

Category	US10CP816206	
Discount Schedule	0CP8	
Gtin	785901039280	
Returnability	Yes	
Country Of Origin	US	

## **Packing Units**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	11.81 in (30.0 cm)	
Package 1 Width	11.73 in (29.8 cm)	
Package 1 Length	14.61 in (37.1 cm)	
Package 1 Weight	33.40 lb(US) (15.15 kg)	

# **Contractual warranty**

Warranty 10 Years



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>②</b>	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov