# **Product data sheet**

Specifications







Transformer, Type T, industrial control, 200VA, 1 phase, 120V primary, 12/24V secondary, 80C rise

9070T200D13

Product availability: Stock - Normally stocked in distribution facility

### Price\*: 352.00 USD

### Main

Product Type	Industrial Control Transformer
Туре	Т

### Complementary

· · · · · · · · · · · · · · · · · ·	
Number Of Phases	1 phase
Power Rating	200 VA UL
	200 VA CSA
	200 VA NOM
	200 VA CE
Primary To Secondary Voltage	120 V 12/24 V
Temperature Rise	80 °C
Electrical Connection	Screw clamp terminals
Height	3.2 in (81.28 mm)
Width	3.75 in (95.25 mm)
Depth	3.59 in (91.19 mm)
Material	Copper: winding
Fingersafe Cover Compatibility	FSC1

## Environment

Certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation Temperature	266 °F (130 °C)

## Ordering and shipping details

Category	US10CP816200
Discount Schedule	0CP8
Gtin	785901313847
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.63 in (14.3 cm)
Package 1 Width	6.34 in (16.1 cm)
Package 1 Length	7.13 in (18.1 cm)
Package 1 Weight	5.94 lb(US) (2.694 kg)

# **Contractual warranty**

Warranty

10 Years

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov