

Product data sheet

Specifications

SQUARE D



Transformer, control disconnect,
3kVA, 1 phase, 240x480V primary,
120V secondary, 115C rise

9070SK3000A2D1E23

⚠ Discontinued on: Jan 2, 2024

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Device Short Name	SK
Enclosure Type	Dust and damp proof enclosure indoor
Product Or Component Type	Power supply source
Provided Equipment	Vario V3 switch-disconnector
Range Of Product	Square D

Complementary

Depth	25.56 in (649.22 mm)
Design	Standard
Device Mounting	Surface
Electrical Connection	Screw clamp terminal
Height	13.49 in (342.65 mm)
Material	Copper: winding
Mounting Support	Panel
Phase	1 phase
Primary Voltage	240 x 480 V
Rated Power In Va	3000 VA
Rated Voltage	120 V auxiliary power supply 120 V isolated
Secondary Voltage	120 V
Temperature Rise	115 °C
Width	16.5 in (419.10 mm)

Environment

Insulation Temperature	356 °F (180 °C)
Nema Degree Of Protection	NEMA 12
Product Certifications	UL listed file E61239 CSA LR37055

Ordering and shipping details

Category	US10CP821694
----------	--------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Discount Schedule	0CP8
Gtin	785901742739
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	87.00 lb(US) (39.463 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	