

# Product data sheet

Specifications

SQUARE D



Transformer, control disconnect,  
3kVA, 1 phase, 240x480V primary,  
120V secondary, 115C rise

9070SK500G1D1F11

⚠ Discontinued on: Jan 2, 2024

⚠ Discontinued

Price\*: 1,607.00 USD

## Main

Device Application	Power supply
Device Short Name	SK
Enclosure Type	Standard environment enclosure indoor
Provided Equipment	Vario V3 switch-disconnector
Range Of Product	Square D

## Complementary

Depth	8.96 in (227.58 mm)
Design	Standard
Device Mounting	Surface
Electrical Connection	Screw clamp terminal
Height	9.4 in (238.76 mm)
Material	Copper: winding
Mounting Support	Panel
Phase	1 phase
Primary Voltage	240 x 480 V
Rated Power In Va	500 VA
Rated Voltage	120 V auxiliary power supply 120 V isolated
Secondary Voltage	120 V
Temperature Rise	115 °C
Width	11.8 in (299.72 mm)

## Environment

Insulation Temperature	356 °F (180 °C)
Nema Degree Of Protection	NEMA 1
Product Certifications	CSA LR37055 UL listed file E61239

## Ordering and shipping details

Category	21694-9070 SK
Discount Schedule	CP8

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Gtin	785901747031
Returnability	No
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.60 in (29.464 cm)
Package 1 Width	11.70 in (29.718 cm)
Package 1 Length	15.20 in (38.608 cm)
Package 1 Weight	29.00 lb(US) (13.154 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability




**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.	
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>	