Product data sheet

Specifications







Transformer, Type T, industrial control, 50VA, 1 phase, 240x480V primary, 120V secondary, 55C rise

9070T50D1SF41

Product availability: Stock - Normally stocked in distribution facility

Price*: 159.00 USD

Main

| Product Type | Industrial Control Transformer |
|--------------|--------------------------------|
| Туре | Т |

Complementary

| Number Of Phases | 1 phase | |
|------------------------------|-------------------|--|
| Power Rating | 50 VA UL | |
| | 50 VA CSA | |
| | 50 VA NOM | |
| | 50 VA CE | |
| Primary To Secondary Voltage | 240 x 480 V 120 V | |
| | 230 x 460 V 115 V | |
| | 220 x 440 V 110 V | |
| Temperature Rise | 55 °C | |

Environment

Enclosure Type

Not rated (open device)

Ordering and shipping details

| Category | US10CP816200 | |
|-------------------|--------------|--|
| Discount Schedule | 0CP8 | |
| Gtin | 785901905424 | |
| Returnability | Yes | |
| Country Of Origin | US | |

Packing Units

| 0 | |
|------------------------------|------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.40 in (13.716 cm) |
| Package 1 Width | 6.20 in (15.748 cm) |
| Package 1 Length | 7.20 in (18.288 cm) |
| Package 1 Weight | 2.50 lb(US) (1.134 kg) |
| Unit Type Of Package 2 | PAL |
| Number Of Units In Package 2 | 150 |

umber Of Units In Package 2

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Package 2 Height | 40.00 in (101.6 cm) |
|------------------|----------------------------|
| Package 2 Width | 40.00 in (101.6 cm) |
| Package 2 Length | 48.00 in (121.92 cm) |
| Package 2 Weight | 432.39 lb(US) (196.128 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |