Product data sheet

Specifications







Transformer, Type T, industrial control, 50VA, 1 phase, 277V primary, 120V secondary, 55C rise

9070T50D4

Product availability: Stock - Normally stocked in distribution facility

Price*: 162.00 USD

Main

Product Type	Industrial Control Transformer
Туре	т

Complementary

Number Of Phases	1 phase	
Power Rating	50 VA UL	
	50 VA CSA	
	50 VA NOM	
	50 VA CE	
Primary To Secondary Voltage	277 V 120 V	
Temperature Rise	55 °C	
Electrical Connection	Screw clamp terminals	
Height	2.58 in (65.53 mm)	
Width	3 in (76.20 mm)	
Depth	3.09 in (78.49 mm)	
Material	Copper: winding	
Fingersafe Cover Compatibility	FSC1	

Environment

Certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation Temperature	221 °F (105 °C)

Ordering and shipping details

Category	US10CP816200
Discount Schedule	0CP8
Gtin	785901905431
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1

PCE

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	4.00 in (10.16 cm)
Package 1 Width	3.80 in (9.652 cm)
Package 1 Length	4.10 in (10.414 cm)
Package 1 Weight	2.53 lb(US) (1.148 kg)

Contractual warranty

Warranty

10 Years

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov