





Transformer, Type T, industrial control, 750VA, 1 phase, 550/575/600V primary, 120/240V secondary, 115C rise

9070T750D37

Product availability: Stock - Normally stocked in distribution facility

Price\*: 1,218.00 USD

#### Main

Product Type	Industrial Control Transformer
Туре	Т

## Complementary

Number Of Phases	1 phase	
Power Rating	750 VA UL	
	750 VA CSA	
	750 VA NOM	
	500 VA CE	
Primary To Secondary Voltage	550/575/600 V 120/240 V	
	550/575/600 V 115/230 V	
	550/575/600 V 110/220 V	
Temperature Rise	115 °C	
Electrical Connection	Screw clamp terminals	
Height	4.51 in (114.55 mm)	
Width	5.25 in (133.35 mm)	
Depth	5.61 in (142.49 mm)	
Fingersafe Cover Compatibility	FSC2	

## **Environment**

Certifications	UL Listed CSA
Enclosure Type	Not rated (open device)
Insulation Temperature	356 °F (180 °C)

## Ordering and shipping details

Category	US10CP816206	
Discount Schedule	0CP8	
Gtin	785901689218	
Returnability	Yes	
Country Of Origin	US	

## **Packing Units**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.80 in (17.272 cm)
Package 1 Width	8.20 in (20.828 cm)
Package 1 Length	8.80 in (22.352 cm)
Package 1 Weight	17.00 lb(US) (7.711 kg)

# **Contractual warranty**

Warranty 10 Years



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov