





Transformer, Type T, industrial control, 3000VA, 1 phase, 600V primary, 120V secondary, 115C rise

9070T3000D5

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,297.00 USD

Main

Product Type	Industrial Control Transformer
Туре	T

Complementary

Number Of Phases	1 phase
Power Rating	3000 VA UL
	3000 VA CSA
	3000 VA NOM
	2000 VA CE
Primary To Secondary Voltage	600 V 120 V
	575 V 115 V
	550 V 110 V
Temperature Rise	115 °C
Electrical Connection	Screw clamp terminals
Height	8.75 in (222.25 mm)
Width	9 in (228.60 mm)
Depth	7.24 in (183.90 mm)
Material	Copper: winding
Fingersafe Cover Compatibility	FSC2

Environment

Certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation Temperature	356 °F (180 °C)

Ordering and shipping details

Category	US10CP816205
Discount Schedule	0CP8
Gtin	785901767923
Returnability	No
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.00 in (33.02 cm)
Package 1 Width	12.00 in (30.48 cm)
Package 1 Length	15.00 in (38.1 cm)
Package 1 Weight	59.70 lb(US) (27.08 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov