# Product data sheet

Specifications







# Industrial control transformer, Type TF, 1 phase, 1000VA, 208/230/460V primary, 115V secondary, 50/60Hz

9070TF1000D20

Product availability: Non-Stock - Not normally stocked in distribution facility

### Price\*: 1,914.00 USD

#### Main

Product Or Component Type	Industrial Control Transformer
Туре	TF
Complementary	/
Number Of Phases	1 phase
Power Rating	1000 VA UL
	1000 VA CSA
	1000 VA NOM

	1000 VA NOM 600 VA CE
Primary To Secondary Voltage	208/230/460 V 115 V
Fuse Type	0.41 x 1.50 in CC top
Temperature Rise	115 °C
Electrical Connection	Screw clamp terminals
Height	7.46 in (189.48 mm)
Width	7.06 in (179.32 mm)
Depth	5.92 in (150.37 mm)
Material	Copper: winding
Fingersafe Cover Compatibility	FSC2

### Environment

Product Certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation Temperature	356 °F (180 °C)

# Ordering and shipping details

Category	US10CP816207
Discount Schedule	0CP8
Gtin	785901149019
Returnability	No
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.00 in (27.94 cm)
Package 1 Width	11.25 in (28.575 cm)
Package 1 Length	14.19 in (36.043 cm)
Package 1 Weight	30.90 lb(US) (14.016 kg)

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov