

Transformer, Type TF, industrial control, 750 VA, 208/277/380 VAC pri / 95/115 VAC sec, 1 phase, 50/60 Hz, 115 °C rise

9070TF750D18

(!) Discontinued on: Jan 2, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Industrial Control Transformer
Туре	TF

Complementary

Number Of Phases	1 phase
Power Rating	750 VA UL 750 VA CSA 750 VA NOM 500 VA CE
Primary To Secondary Voltage	208/277/380 V 95/115 V
Fuse Type	0.41 x 1.50 in CC top
Temperature Rise	115 °C
Electrical Connection	Screw clamp terminals
Height	5.73 in (145.54 mm)
Width	5.25 in (133.35 mm)
Depth	6.04 in (153.42 mm)

Environment

Product Certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation Temperature	356 °F (180 °C)

Ordering and shipping details

Category	US10CP816203
Discount Schedule	0CP8
Gtin	785901470564
Returnability	No
Country Of Origin	IIS

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.50 in (16.51 cm)
Package 1 Width	8.50 in (21.59 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	21.10 lb(US) (9.571 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >


Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov