

Product data sheet

Specifications

SQUARE D



Terminal block, Linergy, fuse holder, Class R, 60A, 250 V, 2 pole

9080FB2221R

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	9080FB
Product	Fuse holder

Complementary

Current Rating	60 A
[Ue] Rated Operational Voltage	<= 250 V AC/DC
Fuse Type	R
Fuse Size	0.8125 x 3 in
Number Of Poles	2
Electrical Connection	Box lugs
Wire Gauge	AWG 14...AWG 2 copper or aluminium
Sccr	200 kA UL 512
Product Certifications	CE UL listed file E40747 CCN IZLT CSA file 70360 class 6225 01
Operating Temperature	-40...257 °F (-40...125 °C)
Mounting Type	Surface mount
Block Material	Thermoplastic: block
Wire Stripping Length	0.5625 in (14.29 mm)
Terminal Tightening Torque	lugs 50 lbf.in (5.65 N.m) AWG 3...AWG 2 copper or aluminium lugs 45 lbf.in (5.08 N.m) AWG 6...AWG 4 copper or aluminium lugs 40 lbf.in (4.52 N.m) AWG 8 copper or aluminium lugs 35 lbf.in (3.95 N.m) AWG 12...AWG10 copper or aluminium lugs 35 lbf.in (3.95 N.m) AWG 14 copper
Height	4.83 in (122.68 mm)
Width	2.86 in (72.64 mm)
Depth	2.01 in (51.05 mm)

Ordering and shipping details

Category	US10CP121701
Discount Schedule	0CP1
Gtin	785901097822
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	US
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.00 in (5.08 cm)
Package 1 Width	2.80 in (7.112 cm)
Package 1 Length	4.80 in (12.192 cm)
Package 1 Weight	6.72 oz (190.509 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration	Pro-active China RoHS declaration (out of China RoHS legal scope)
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	