

(!) Discontinued

Transformer, Type TF, industrial control, 1000 VA, 208/277/380 VAC pri / 95/115 VAC sec, 1 phase, 50/60 Hz, 115 °C rise

9070TF1000D18

(!) Discontinued on: Jan 2, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Or Component Type	Industrial Control Transformer
Туре	TF

## Complementary

Number Of Phases	1 phase	
Power Rating	1000 VA UL 1000 VA CSA 1000 VA NOM 600 VA CE	
Primary To Secondary Voltage	208/277/380 V 95/115 V	
Fuse Type	0.41 x 1.50 in CC top	
Temperature Rise	115 °C	
Electrical Connection	Screw clamp terminals	
Height	7.46 in (189.48 mm)	
Width	7.06 in (179.32 mm)	
Depth	5.81 in (147.57 mm)	
Material	Copper: winding	
Fingersafe Cover Compatibility	FSC2	

### **Environment**

Product Certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation Temperature	356 °F (180 °C)

### Ordering and shipping details

Category	US10CP816207	
Discount Schedule	0CP8	
Gtin	785901934172	
Returnability	No	
Country Of Origin	US	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.00 in (27.94 cm)
Package 1 Width	11.25 in (28.575 cm)
Package 1 Length	14.19 in (36.043 cm)
Package 1 Weight	32.00 lb(US) (14.515 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov