


Product data sheet

Specifications



Terminal block, Linergy, circuit isolation switch, natural color, 30A, 600 V

9080GG6

! Discontinued

! Discontinued on: Nov 11, 2020

! End-of-service on: Dec 31, 2020

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	9080G
Product Type	Terminal block
Localisation On Device	Circuit isolating switch
Color	Natural
Quantity	Set of 10

Complementary

Voltage Rating	600 V AC/DC
Current Rating	30 A UL 30 A CSA
Wire Size	AWG 18...AWG 10 copper
Mounting Type	9080GH track 35 mm DIN rail
Certifications	CE UL recognized E60616 CCN XCFR2 CSA file 62144 class 6228 01
Electrical Connection	pressure wire clamp
Material	Nylon: block Tin plated copper: busbar
Ambient Air Temperature For Operation	-40...257 °F (-40...125 °C)
Electrical Connrection Tightening Torque	Clamp terminal zinc plated steel 18...20 lbf.in (2.03...2.26 N.m) : AWG 18...AWG 10 copper)
Height	2.07 in (52.58 mm)
Width	2.19 in (55.63 mm)
Depth	0.76 in (19.30 mm)
Density	16 per foot
Compatible End Barrier	GF6B

Ordering and shipping details

Category	US10CP521702
Discount Schedule	0CP5

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Gtin	00785901155058
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability






Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 RoHS Exemption Information	Yes
 Pvc Free	
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov