Specifications



Transformer, Type TF, industrial control, 250 VA, 208/277/380 VAC pri / 95/115 VAC second, 1 phase, 50/60 Hz, 80 °C rise

9070TF250D18

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,026.00 USD

Main

Product Or Component Type	Industrial Control Transformer
Туре	TF

Complementary

· · · · · · · · · · · · · · · · · ·		
Number Of Phases	1 phase	
Power Rating	250 VA UL	
	250 VA CSA	
	250 VA NOM	
	160 VA CE	
Primary To Secondary Voltage	208/277/380 V 95/115 V	
Fuse Туре	0.41 x 1.50 in CC top	
Temperature Rise	80 °C	
Electrical Connection	Screw clamp terminals	
Height	5.1 in (129.54 mm)	
Width	4.5 in (114.30 mm)	
Depth	5.09 in (129.29 mm)	
Material	Copper: winding	

Environment

Product Certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation Temperature	266 °F (130 °C)

Ordering and shipping details

Category	US10CP816207
Discount Schedule	0CP8
Gtin	785901545019
Returnability	No
Country Of Origin	US

Packing Units

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.00 in (15.24 cm)
Package 1 Width	7.50 in (19.05 cm)
Package 1 Length	6.50 in (16.51 cm)
Package 1 Weight	8.80 lb(US) (3.992 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov