


Product data sheet

Specifications

SQUARE D



Terminal block, Linergy, box lug connector, orange colored block, 60A, 600 V

9080GRS6

Product availability: Stock - Normally stocked in distribution facility

Price*: 2.40 USD

Main

Range Of Product	9080G
Product Type	Terminal block
Localisation On Device	Standard
Color	Orange
Quantity	Set of 50

Complementary

Voltage Rating	600 V AC/DC
Current Rating	60 A UL 60 A CSA
Wire Size	AWG 22...AWG 8 copper
Mounting Type	9080GH track 35 mm DIN rail
Certifications	UL recognized E60616 CCN XCFR2 CE CSA file 62144 class 6228 01
Protection Type	Fingersafe DIN 57470
Electrical Connection	Copper box lugs
Material	Nylon: block
Ambient Air Temperature For Operation	-40...257 °F (-40...125 °C)
Electrical Connrection Tightening Torque	Lug copper 18...20 lbf.in (2.03...2.26 N.m) : AWG 22...AWG 8 copper)
Height	1.82 in (46.23 mm)
Width	1.72 in (43.69 mm)
Depth	0.35 in (8.89 mm)
Density	34 per foot
Compatible End Barrier	GM6B

Ordering and shipping details

Category	US10CP521702
Discount Schedule	0CP5
Gtin	785901058793
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	MX
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

<div>✓</div>	Reach Free Of Svhc	
<div>✓</div>	Toxic Heavy Metal Free	
<div>✓</div>	Mercury Free	
<div>✓</div>	Rohs Exemption Information	Yes
<div>✓</div>	Pvc Free	
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	