

Product data sheet

Specifications

SQUARE D



NEMA Motor Starter and contactor, Type S, auxiliary contact, 1 NO/1 NC isolated contact, external, field convertible

9999SX8

Product availability: Stock - Normally stocked in distribution facility

Price*: 116.00 USD

Main

Product Range	Type S
Component Type	Auxiliary Contact Module
Used With	contactor starter

Complementary

Nema Size	3
	4
	00
	1
	6
	2
	5
	7
	0
Auxiliary Contact Composition	1 NO + 1 NC
[Uc] Control Circuit Voltage	<= 600 V AC 50/60 Hz
Rated Breaking Capacity	6 A 120 V AC inductive control circuit UL 508 3 A 240 V AC inductive control circuit UL 508 1.2 A 600 V AC inductive control circuit UL 508 1.5 A 480 V AC inductive control circuit UL 508 10 A <= 600 V AC resistive control circuit UL 508
Height	1.5 in (38.10 mm)
Width	3 in (76.20 mm)
Depth	4.5 in (114.30 mm)
Net Weight	0.31 lb(US) (0.14 kg)

Environment

Product Certifications	CSA UL Recognized UL Listed
------------------------	-----------------------------------

Ordering and shipping details

Category	US10CP121761
Discount Schedule	0CP1
Gtin	785901733539
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	MX
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.50 in (3.81 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	4.70 in (11.938 cm)
Package 1 Weight	4.96 oz (140.614 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	6.00 in (15.24 cm)
Package 2 Width	6.80 in (17.272 cm)
Package 2 Length	8.00 in (20.32 cm)
Package 2 Weight	3.00 lb(US) (1.361 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Reach Regulation	REACH Declaration
Eu Rohs Directive	Not compliant
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov