
Product data sheet

Specification







A9XPH306

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 55.00 USD

Main

Range	Acti9
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	3L
Length In 18 Mm Modules	6

Complementary

Number Of Ways	2 ways 3 L
Poles Configuration For 1 Way	1 x 3P
Connection Pitch	0.71 in (18 mm)
Connector Type	tooth
Distance Between Way	2.13 in (54 mm)
Marking	L1 L2 L3
Insulation	Insulated
Device Presentation	Cuttable
[le] Rated Operational Current	100 A 104 °F (40 °C)
[Ue] Rated Operational Voltage	415 V AC
[Ui] Rated Insulation Voltage	500 V AC IEC 61439-2
Mounting Location	Top or bottom tunnel type terminals Top or bottom double terminal
9 Mm Pitches	12
Width	4.33 in (110 mm)
Color	White RAL 9003)
Range Compatibility	Acti 9 Acti9 iC60 Acti 9 Acti9 iK60 Acti 9 Acti9 iID Acti 9 Acti9 iID K Acti 9 Acti9 iSW Acti 9 Acti9 iSW Acti 9 Multi9 Multi9 C60

Environment

Standards	IEC 60947-7-1	
	IEC 61439-2	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Fire Resistance	1760 °F (960 °C) 30 s) IEC 60695-2-1
Pollution Degree	3 IEC 60947-7-1
Ip Degree Of Protection	IP20 with end-pieces and tooth covers

Ordering and shipping details

Category	US10DE200908
Discount Schedule	0DE2
Gtin	3606480747953
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.63 in (1.600 cm)
Package 1 Width	1.18 in (3.000 cm)
Package 1 Length	4.33 in (11.000 cm)
Package 1 Weight	1.59 oz (45.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	2.17 in (5.500 cm)
Package 2 Width	3.35 in (8.500 cm)
Package 2 Length	9.65 in (24.500 cm)
Package 2 Weight	18.17 oz (515.000 g)
Unit Type Of Package 3	S02
Number Of Units In Package 3	80
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	9.77 lb(US) (4.430 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations