

Product data sheet

Specifications



connecting cable - Advantys Telefast - 3m - 32 O 100 mA - for Allen Bradley

ABFH40H301

⚠ Discontinued on: May 2, 2022

⚠ Discontinued

Main

Accessory / Separate Part Destination	Allen Bradley PLC
Range Of Product	Advantys Telefast
Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Type	Connection cable
Accessory / Separate Part Designation	Connecting cable
Number Of Channels	16

Complementary

Product Compatibility	SLC500
Cable Length	9.84 ft (3 m)
Type Of Signal	100 mA 32 channel output
Electrical Connection	1 connector HE10, 40 ways PLC side 2 connectors HE10, 20 ways Telefast end
Awg Gauge	AWG 22
Wire Section	0.00 in² (0.324 mm²)

Ordering and shipping details

Category	22375-INTERFACE MODULE(ABA,R,S)
Discount Schedule	CP2
Gtin	3389110705478
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.77 in (4.5 cm)
Package 1 Width	9.45 in (24 cm)
Package 1 Length	9.45 in (24 cm)
Package 1 Weight	32.06 oz (909 g)

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov