





# End tap box, I-Line Busway, max 2000A rated, aluminum, bolt connection, 3 wire

AF2320GETBMB

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 12,351.30 USD

#### Main

Product	End tap box
Range	I-Line

## **Complementary**

Rated Current	2000 A aluminium
Rated Operational Voltage	600 V AC/DC 50/60 Hz
Length	29.14 in (740.16 mm)
Height	28 in (711.20 mm)
Width	16.88 in (428.75 mm)
Material	Aluminium: busbar
I-Line Value End	Bolt
Number Of Phases	3 phase
For Use With	Busbar trunking 2000 A aluminium
Protection Type	50 percent capacity integral ground bus
Wiring Configuration	3-wire

#### **Environment**

Standards	UL 857	
	CSA C22.2 No 27:1994	
	IEC 61439-6	

## Ordering and shipping details

Category	US10PE820262
Discount Schedule	0PE8
Gtin	785901815785
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	29.13 in (74.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	16.89 in (42.9 cm)
Package 1 Length	27.99 in (71.1 cm)
Package 1 Weight	172.00 lb(US) (78.018 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>②</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>②</b>	Pvc Free

#### **Certifications & Standards**

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov