





End tap box, I-Line Busway, max 1600A rated, aluminum, bolt connection, 4 wire

AF2516GETBMB

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 13,184.30 USD

Main

Product	End tap box
Range	I-Line

Complementary

Rated Current	1600 A aluminium	
Rated Operational Voltage	600 V AC/DC 50/60 Hz	
Length	29.14 in (740.16 mm)	
Height	28 in (711.20 mm)	
Width	14.88 in (377.95 mm)	
Material	Aluminium: busbar	
I-Line Value End	Bolt	
Number Of Phases	3 phase	
For Use With	Busbar trunking 1600 A aluminium	
Protection Type	50 percent capacity integral ground bus	
Wiring Configuration	4-wire	

Environment

Standards	UL 857	
	CSA C22.2 No 27:1994	
	IEC 61439-6	

Ordering and shipping details

Category	US10PE820010	
Discount Schedule	0PE8	
Gtin	785901815884	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	29.13 in (74.0 cm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	14.88 in (37.8 cm)	
Package 1 Length	27.99 in (71.1 cm)	
Package 1 Weight	175.00 lb(US) (79.379 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information Ye	s
9	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov