





Adaptor - I-Line - 2000A - 4W - slot - AI - 12.00in

AF2520G12S

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 9,648.91 USD

Main

Product	Adaptor
Range	I-Line

Complementary

Rated Current	2000 A aluminium
Rated Operational Voltage	600 V AC/DC 50/60 Hz
Length	12 in (304.80 mm)
Material	Aluminium: busbar
I-Line Value End	Slot
Number Of Phases	3 phase
For Use With	Busbar trunking 2000 A aluminium
Protection Type	50 percent capacity integral ground bus
Wiring Configuration	4-wire
Mounting Location	Indoor

Environment

Standards	UL 857
	CSA C22.2 No 27:1994
	IEC 61439-6

Ordering and shipping details

Category	US10PE820012
Discount Schedule	0PE8
Gtin	785901016847
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.88 in (14.935 cm)
Package 1 Width	12.72 in (32.309 cm)
Package 1 Length	13.00 in (33.02 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Weight

59.50 lb(US) (26.989 kg)

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation

Eu Rohs Directive	Compliant
Eu Rons Directive	'
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

REACh Declaration