

# Product data sheet

Specifications

## Cover for cable duct - Width=60mm

AK2CA6



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 23.60 USD

### Main

Product Or Component Type	Cover
Accessory / Separate Part Category	Cabling accessories
Range Compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Mounting Support	Cable duct 2.36 in (60 mm)
Quantity Per Set	Set of 8

### Complementary

Color	Blue RAL 5000)
Length	78.74 in (2000 mm)
Width	2.36 in (60 mm)
Material	PVC (polyvinyl chloride)
Net Weight	0.95 lb(US) (0.43 kg)

### Environment

Ambient Air Temperature For Operation	23...140 °F (-5...60 °C)
Flame Retardance	V-0 UL 94
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 VDE 0660

### Ordering and shipping details

Category	US1000I22622
Discount Schedule	000I
Gtin	3389110570267
Returnability	No
Country Of Origin	FR

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	0.39 in (1.0 cm)
Package 1 Width	3.94 in (10.0 cm)
Package 1 Length	78.74 in (200.0 cm)
Package 1 Weight	16.12 oz (457.0 g)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	1120
Package 2 Height	42.52 in (108.0 cm)
Package 2 Width	79.13 in (201.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	1316.16 lb(US) (597.0 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	8
Package 3 Height	79.13 in (201.0 cm)
Package 3 Width	4.53 in (11.5 cm)
Package 3 Length	2.56 in (6.5 cm)
Package 3 Weight	8.91 lb(US) (4.04 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability





**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
<b>Reach Regulation</b>		<a href="#">REACH Declaration</a>
<b>Eu Rohs Directive</b>		Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<b>China Rohs Regulation</b>		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)