


# Product data sheet

Specifications

## Cable duct - 75 x 125 mm - without cover - grey



AK2GD12575

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 88.50 USD

### Main

Product Or Component Type	Cable duct
Accessory / Separate Part Category	Cabling accessories
Range Compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device Composition	Without cover
Quantity Per Set	Set of 8

### Complementary

Color	Gray RAL 7030)
Fixing Mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	2.95 in (75 mm)
Length	78.74 in (2000 mm)
Width	4.92 in (125 mm)
Net Weight	3.00 lb(US) (1.36 kg)
Total Number Of Wires	700

### Environment

Ambient Air Temperature For Operation	23...140 °F (-5...60 °C)
Flame Retardance	V-0 UL 94
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	VDE 0660 VDE 0506 DIN 43659

### Ordering and shipping details

Category	US1000I22622
Discount Schedule	000I
Gtin	3389110570496
Returnability	Yes
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.91 in (15.0 cm)
Package 1 Width	10.24 in (26.0 cm)
Package 1 Length	78.74 in (200.0 cm)
Package 1 Weight	3.31 lb(US) (1.5 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	72
Package 2 Height	30.31 in (77.0 cm)
Package 2 Width	110.24 in (280.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	317.47 lb(US) (144.0 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	8
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	10.24 in (26.0 cm)
Package 3 Length	78.74 in (200.0 cm)
Package 3 Weight	26.46 lb(US) (12.0 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)