Product data sheet

Specifications





Plug outlet, Linergy HK, 1P+N, 32A, 1 point, 4 mm², cable length 1000mm

AK5PC32L

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 28.10 USD

Main

Range	Linergy
Product Name	НК
Product Or Component Type	Plug outlet
Poles Description	1P + N
[Ith] Conventional Free Air Thermal Current	32 A
I ² T On Activation	200000 A².s
Number Of Points	1
Number Of Cables	2 0.01 in² (4 mm²)
Cable Length	3.28 ft (1 m)
Quantity Per Set	Set of 6

Complementary

[Ui] Rated Insulation Voltage	600 V CSA 600 V UL 690 V IEC 60439-1
Peak Current	25 kA
Width	0.71 in (18 mm)
Height	1.81 in (46 mm)
Depth	1.50 in (38 mm)
Net Weight	0.09 lb(US) (0.04 kg)

Environment

Standards	IEC 60439
Product Certifications	DNV UL CSA LROS (Lloyds register of shipping)

Ordering and shipping details

Category	US10I1122623
Discount Schedule	0 11
Gtin	3389110576849
Returnability	No

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country	Of	Origin
---------	----	--------

Packing Units

r adning offics	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.54 in (9.000 cm)
Package 1 Width	9.25 in (23.500 cm)
Package 1 Length	9.25 in (23.500 cm)
Package 1 Weight	3.46 oz (98.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	3.54 in (9.000 cm)
Package 2 Width	9.25 in (23.500 cm)
Package 2 Length	9.25 in (23.500 cm)
Package 2 Weight	24.06 oz (682.000 g)
Unit Type Of Package 3	S04
Number Of Units In Package 3	54
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	15.75 in (40.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	14.87 lb(US) (6.746 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations